



PS-200

DESCRIPTION

The PS-200 measures a wavelength range of 300 to 850 nm. The spectroradiometer comes in a complete package ready to connect to your computer and begin making measurements. Typical applications include measurement of spectral output (energy flux density, photon flux density, or illuminance) of different radiation sources (often for plant or human lighting), and reflectance and transmittance measurements of natural and synthetic surfaces and materials (often plant leaves and canopies).



Features:

Three Wavelength Options

350 to 1000 nm, 300 to 830 nm, or 300 to 1000 nm.

Complete Package

Includes spectroradiometer, two meter fiber-optic cable, cosine corrected detector, USB cable, USB drive with required drivers and software (compatible with all 32-bit and 64-bit Windows operating systems), and shoulder bag (functions as a carrying case and field measurement pack). A reflectance probe and reflectance standard are available as accessories.

Portable Field Measurements

Features a small and lightweight design with a rugged housing and no moving parts. Spectroradiometer is powered through the USB port on a computer allowing mobile field measurements.

Typical Applications

Measurement of spectral output of radiation sources for plant or human lighting, reflectance and transmittance measurements of natural and synthetic surfaces and materials (often plant leaves and canopies), and absorbance measurements of chemical samples.

THE PS-200 PACKAGE

INCLUDES:

1. Spectroradiometer unit
2. Fiber optic cable (2 m)
3. Apogee cosine corrected radiometric head with black cap
4. Apogee bubble level plate
5. Apogee calibration (certificate upon request)
6. Apogee 2GB USB drive with data collection software and calibration files
7. Blue USB 2.0 cable
8. Apogee carrying case
9. Reflectance wand
10. 1 year warranty

PS-200

	PS-100	PS-200	PS-300
Irradiance Calibration Range	350 to 1000 nm	300 to 850 nm	300 to 1000 nm
Wavelength Sensitivity	350 to 1150 nm	190 to 850 nm	220 to 1100 nm
Detector Type	CCD, 2048 pixel		
Grating Type	Holographic & Ruled, 600 g/nm	Holographic and aberration-corrected, 590 g/nm	
Digitizer	16-bit		
Signal to Noise Ratio	1000:1		
Stray Light	0.1 % at 435 nm, 0.5 % at 600 nm	0.02 % at 435 nm, 0.2 % at 200 nm	0.02 % at 435 nm, 0.2 % at 220 nm
Measurement Repeatability	Less than 1 %		
Irradiance Calibration Uncertainty	± 10 %		
Detector Integration (Exposure) Range	1 ms to 65 s		
Directional (Cosine) Response	± 5 % at 80° zenith angle		
Software	Windows compatible, included		
Computer Interface	USB 2.0		
Power Requirement	100 mA at 5 V DC, supplied via USB code		
Operating Temperature	0 to 60 C		
Optical Cable	2 m armored fiber-opt		
Base Unit Size	25 mm x 75 mm x 125 mm	69 mm x 100 mm x 150 mm	
Mass	500 g	900 g	
Warranty	1 year against defects in materials and workmanship		

Contact info



Monitoring MENA

Insight into instrumentations

(962) 5353-2091

PO Box 1100 Salt

Post Code 19110 JORDAN

sales@monitoring-mena.com

www.monitoring-mena.com



This Instrument is manufactured by our principle company

Apogee Instruments - USA