

SS-110

DESCRIPTION

The SS-110 measures a wavelength range of 340 to 820 nm. The spectroradiometer is an easyto-use, cost-effective, versatile spectral measurement system that can be interfaced to a computer. Typical applications include measurement of spectral output (energy flux density, photon flux density, or illuminance) of different radiation sources (often for plant or human lighting), and reflectance and transmittance measurements of natural and synthetic surfaces and materials (often plant leaves and canopies).



Features:

Wavelength Range Options

Two wavelength range options are available: 340 to 820 nm (SS-110) and 635 to 1100 nm (SS-120).

Portable Design

The Field Spectroradiometer is small and lightweight, and contains all measurement components in a durable, weatherproof housing.

Spectral Measurements

Lighting quality is just as important as lighting quantity. In addition to measuring total PPFD, the new Field Spectroradiometer splits light to individually measure each color intensity or wavelength. Spectral output measurements can be used to maximize light efficiency, change the light characteristics to mimic seasonal changes, optimize visual appearance of displays, and many other applications.

Complete Package

Package includes spectroradiometer and cosine-corrected detector mounted in the housing, 180° FOV head, AL-200 bubble-level, USB cable for computer interface, and USB drive with required drivers and software (windows compatible, XP and later; Mac compatible 10.9 and later), and carrying case.

Field of View Options

Three field of view (FOV) options are available: 180° FOV hemispherical head for measurement of incoming radiation (included), and 150° FOV wide (AS-010 accessory) and 25° FOV narrow (AS-011 accessory) to measure reflected radiation.

Typical Applications

Measurement of spectral output (energy flux density, photon flux density, or illuminance) of different radiation sources (often for plant or human lighting), and reflectance and transmittance measurements of natural and synthetic surfaces and materials (often plant leaves and canopies).

SS-110

THE SS-110 PACKAGE INCLUDES:

- Spectroradiometer unit and cosine corrected detector mounted in the housing
- 2. 80° FOV head and black cap
- 3. AL-200 bubble-level
- 4. USB cable for computer interface
- 2GB USB drive with ApogeeSpectrovision software (Windows compatible, XP and later; Mac compatible, 10.10 and later) and required drivers
- 6. Carrying case

Wavelength Range	340 to 820 nm	635 to 1100 nm
Wavelength		
Measurement	1.0 nm	
Internal		
Wavelength Resolution	3.0 nm	
Wavelength Accuracy	± 0.5 nm	
Wavelength Repeatability	± 0.2 nm	
Analog to Digital	14 bit	
Resolution		
Signal to Noise Ratio	1500:1 (at maximum signal)	
Stray Light	≤ 0.25 % at 590 nm	≤ 0.25 % at 850 nm
Dark Noise	≤ 3 counts	
Integration Time Range	10 ms to 10 s	
Measurement Sensitivity	Greater than 10 % of max	Greater than 10 % of max
	sensitivity for	sensitivity for
	wavelengths	wavelengths
	greater than 380 nm	less than 1030 nm
Measurement	Less than 1.0 %	Less than 1.0 %
Repeatability	(wavelengths	(wavelengths
	greater than 400 nm)	less than 1020 nm)
Directional (Cosine)	± 5 % at 75° zenith angle	
Response		
Fields of View	180° (upward-facing); 25° or 150° (downward-facing)	
Temperature Response	-0.1 ± 0.1 % per C	
Irradiance Calibration	±5%	
Uncertainty		
Current Draw	190 mA (USB)	
Power Requirement		
Interface Cable	5 m jacket with USB (for computer)	
Software	Apogee Spectrovision (windows compatible, XP and	
	later; Mac compatible 10.9 and later)	
Operating Environment	-20 to 70 C, 0 to 100% relative humidity	
Thread Size (for	1⁄4"-20	
Mounting)		
Dimensions	89.3 mm height, 50.8 mm width, 38.1 depth	
Mass	300 g	
Warranty	arranty 1 year against defects in materials and workmanship	

Contact info



Monitoring MENA Insight into instrumentations

(962) 5353-2091

PO Box 1100 Salt

Post Code 19110 JORDAN

sales@monitoring-mena.com

www.monitoring-mena.com



This Instrument is manufactured by our principle company Apogee Instruments - USA